

Note:

1. The length L is customized
2. Polarity: Crossover A-B, B-A.
3. RoHS 2.0 And Reach Compliant

**MATERIAL LIST:**

⑦	LC Uniboot Boot White	2pcs	
⑥	Pull rod Aqua	2pcs	
⑤	LC Uniboot Clip Aqua	4pcs	
④	LC Uniboot Connector Aqua	4pcs	
③	LC/UPC Ferrule	2pcs	
②	LC Dust Cap White	4pcs	
①	Fiber Optical Cable Duplex $\phi$ 2.0 MM OM3 LSZH (one tube with 2 fiber) Aqua color	L	
NO.	SPECIFICATION STANDARD	QT' Y	REMARK

TYPE	MULTI-MODE
Insertion LOSS	$\leq 0.3$ dB
Return LOSS	N/A
Test Wavelength	850nm


		NEW	2018-10-26	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

SYNERGY 21					
CUSTOMER		ITEM NO.	See The Chart		
PRODUCT NAME	LC-LC Uniboot OM3 Switchable Patch Cords 2.0	Manufacture country	CHINA	UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE		
SYNERGY 21	SYNERGY 21		2018-10-26		

Chart:

NO.	ITEM NO.	LENGTH.
1	S215540	0.5m
2	S215541	1m
3	S215542	1.5m
4	S215543	2m
5	S215544	3m
6	S215545	5m
7	S215546	7.5m
8	S215547	10m
9	S215548	15m
10	S215549	20m
11		25m
12		30m

PACKING DRAW



Label

PACKING:SYNERGY 21 PE BAG+LABEL

SYNERGY 21									
CUSTOMER					ITEM NO.		See The Chart		
PRODUCT NAME		LC-LC Uniboot OM3 Switchable Patch Cords 2.0			Manufacture country		CHINA	UNIT	MM
DRAWNBY		CHECKBY		APPOBY		DATE			
SYNERGY 21		SYNERGY 21				2018-10-26			

		NEW		2018-10-26	A
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.

# SYNERGY 21


## LC Uniboot Connector Switch Polarity Manual

### — How to guide


1 Get ready to switch




2 Open buckle



3 Shell separated



4 Rotate the spare parts A & B



5 Spare parts rotate 180°



6 Shell rotate 180°



7 Push back shell



8 Assemble push-pull knob

